

### Eyepieces

Micrometer (ø 24 t = 1.5 mm)

- WHSZ10X-H, WHSZ15X-H, WHSZ20X-H, WHSZ30X-H Eyepiece
- WHSZ10X, WHSZ20X Eyepiece

### Camera adapter

DIGITAL CAMERA

- U-TV0.25XC C-mount video port with 0.25x lens
- U-TV0.35XC-2 C-mount video port with 0.35x lens
- U-TV0.5XC-3 C-mount video port with 0.5x lens
- U-TV0.63XC C-mount video port with 0.63x lens
- U-CMAD3 C-mount adapter
- U-TV1X-2 Direct image video port 1x

### SZX7 Observation tubes

- SZX-BI45 Binocular tube
- SZX-BI30 Binocular tube
- SZX-TBI Tilting binocular tube
- SZX2-TR30 Trinocular tube
- SZX2-TTR Tilting trinocular tube

### PHOTO SYSTEM Intermediate tubes

- SZX-PHA Photo adapter
- SZX2-LBS Beam splitter
- SZX2-ILLC10 Coaxial reflected light illuminator
- SZX-DA Macro tube
- SZX-AS AS unit
- SZX-EPA Eyepoint adjuster
- KL-BL245-ILLC Two-armed flexible light guide
- SZX-ZB7 7x microscope zoom body
- SZX2-AN Rotatable analyser
- DFPL0.5X4, DFPL0.75X4, DFPLAPO1X-4, DFPLAPO1.25X, SZX-ACH1X, SZX-ACH1.25X-2, DFPL1.5X4, DFPL2X4 Objective lens
- SZX2-ET Auxiliary sleeve

### Arms

- SZ2-ST5 Arm for SZX stand
- SZ2-STB1 Bonder arm
- SZ2-STB2 Bonder arm
- SZ2-STB3 Bonder arm
- SZ2-STP Prober arm
- SZ-STLA Adapter for SZ-STL

### Stands

- SZX2-ILLD BF/DF transmitted light illumination base
- SZX2-ILLK Transmitted light illumination base
- SZH-P600\*2 600 mm pillar
- SZH-P400\*2 400 mm pillar
- SZX-R Drop prevention collar
- SZ-STL Large-size microscope stand
- SZX2-STU1 Type 1 universal stand
- SZX2-STU3 Table clamp stand
- KL1500-LCD Light source, 150 W
- KL2500-LCD Light source, 250 W
- KL1500-C Light source, 150 W
- U-LS30-5 6 V/30 W lamp socket
- SZX-TLGAD Transmitted light guide adapter
- KL-BL18TL-2 One-armed flexible light guide

### SZ61/SZ51

- SZ61TR Microscope body
- SZ61-60 SZ51-60 Microscope body
- SZ61 SZ51 Microscope body
- SZ-POL-2 Polariser Analyser
- 110ALK0.3X, 110ALK0.4X, 110AL0.5X, 110AL0.62X\*, 110AL0.75X, 110AL1.5X, 110AL2X Auxiliary objective lens
- SZ2-ET Auxiliary sleeve

### Accessories

- U-SRP, U-SRG2 Rotary stage
- SZX-STAD1 Type 1 BX stage adapter
- SZH-SC Cup stage
- SZH-SG Gliding stage
- SZH-CLJ Jewel observation clip
- SZX-PO Simple polariser
- SZ2-SPBW Stage plate
- BH2-SH Horizontal knob stage
- SZH-STAD1 Stage adapter
- SZ2-FO Up/down moving stage

### Lighting and Stands

- SZ2-SPBW Stage plate
- SP-C Stage glass
- SZ2-ST Standard stand
- SZ2-ILST LED illuminator stand
- SZ2-ILA Transmitted illumination attachment
- SZ2-TLGAD Transmitted light guide adapter
- SZ2-LGCL Collector lens
- KL200-BL145/600-ILA Flexible single light guide
- SZ2-LHAD Lamp housing adapter
- U-LH100-3 100 W halogen lamp housing
- TH4\* Power supply
- STX-stands\*3 Pillar
- STX-BASE-1 Base plate
- STX-BASE-2 Base for table mount
- STX-BASE-3 Base for wall mount
- STX-BASE-4 Base with grommet

### EasyLED illumination\*1

- EL-TL Transmitted light LED system
- EL-SL Spotlight LED system
- EL-RL Ring light LED system
- Transmitted light stage with integrated controller
- Controller
- Spotlight
- Ring light with integrated controller
- EL-GA-SZX Gooseneck arm for SZX stands
- EL-GA-SZ Gooseneck arm for SZ stands and bonder arms

### Fibre illumination

- KL200-BL145/600-ILA One-armed flexible light guide
- KL200-SHL135/500 One-armed gooseneck light guide
- KL200-BL245/500-ILLC Two-armed flexible light guide
- KL200-SHL235/500 Two-armed gooseneck light guide
- KL200-6PRL-5/1000 6-point ring light
- SZ2-LGHL Light guide holder
- SZ2-LGCL Collector lens
- SZ2-ILLC Coaxial illuminator
- KL-RA-SZX2 Ring light guide adapter for SZX2
- KL-RA-SZ2 Ring light guide adapter for SZ2
- SZ2-LGB-AD Adapter
- SZ2-LGB Light guide illuminator

\*1 Please consult the Stereo Microscope Lighting Systems brochure for more information  
 \*2 SZH-P400 and SZH-P600 can be attached to the transmitted illumination light bases  
 \*3 Please consult the Stereo Microscope Stands brochure for more information

ESD-compatible